

# BC210 / BC212 / BC410 – QUICK INSTALLATION GUIDE & OVERVIEW

**Congratulations on the purchase of your BC210/BC212 or BC410 speaker cabinet!**

Though connecting and setting up BC210/BC212/BC410 speaker cabinets is easy and straightforward, we recommend reading this installation guide before usage. Enjoy!

## Examples of Cabinet Combinations



### 2x210 speakers stacked

Plenty of low-end and power with the precise, fast and defined tone usually associated with 10" speakers



### 1x212 + 2x210

For a combination of precision, full body and even more low-end from the 2x12" cabinet



### 2x410

The Classic 8x10 from a combination of 2x410. Snappy and crisp with plenty of muscle



### 410 + 212

Cool combination for full low end, precision and body



For the safety of your fellow musicians and your own, please address the stability of stacked cabinets and take proper precautions to prevent the stack from being unstable or tipping over. Also notice that only two cabinets should be stacked vertically.



## Speaker Connections

The Speakon connectors can be used for both input and link. Connect the amp output to one of the connectors and link to a second cabinet using the other connector.

## Please notice the following:

Impedance for BC210, BC212 is 8 Ohm  
Impedance for BC410 is 4 Ohm

All TC Electronic bass amplifiers can run any combination of up to three TC Electronic 8 Ohm cabinets, or up to two 8 Ohm cabinets of another brand.

Depending on the TC Electronic amplifier model, a BC410 (4 Ohm) cabinet can be combined with one or two other cabinets. Please refer to our speaker configuration guide located at [www.tcelectronic.com/cabconfig](http://www.tcelectronic.com/cabconfig)



Should you by accident connect a non-valid combination of cabinets to TC Electronic bass amplifiers, the amps protection mode may be invoked. However, the amplifier will not be damaged.

## Specifications

- Eminence custom drivers (210 = 2x10", 212 = 2x12" 410 = 4x10")
- Tweeter: Eminence 33 mm Titanium Diaphragm
- Power handling: 210 & 212: 250W 410: 500W
- 15 mm plywood
- Handcrafted wooden box
- Tolex covered
- Metal grill
- Rear ported

## Dimensions & Weight

210: WxHxD - 462x662x380 mm  
Weight - 19 kg / 41.6 lbs  
212: WxHxD - 462x662x380 mm  
Weight - 20 kg / 43.8 lbs  
410: WxHxD - 594 x 662 x 426 mm  
Weight - 27 kg / 59.1 lbs

*Subject to change without notice*

## IMPORTANT SAFETY INSTRUCTIONS

- Read these instructions.
- Keep these instructions.
- Heed all warnings.
- Follow all instructions.
- Do not use this apparatus near water.
- Clean only with dry cloth.
- Only use attachments/accessories specified by the manufacturer.



Use only with the cart, stand, tripod, bracket, or table specified by the manufacturer, or sold with the apparatus. When a cart is used, use caution when moving the cart/apparatus combination to avoid injury from tip-over.

### Caution

- You are cautioned that any change or modifications not expressly approved in this manual could void your authority to operate this equipment.

### Service

- There are no user-serviceable parts inside.
- All service must be performed by qualified personnel.